



ZEBRA DS4308-HC

PROTECT PATIENT HEALTH WITH NEXT GENERATION BAR CODE SCANNING

IMPROVE PATIENT SAFETY AND INCREASE CAREGIVER PRODUCTIVITY WITH NEXT GENERATION SCANNING.

Bar code scanning at patient bedside is crucial in preventing medication and specimen mixups — two of the potentially deadliest errors in a hospital. But scanning bar codes in a hospital can be a challenge. There are many types of bar codes including traditional paper-based, those displayed on an electronic screen, codes printed on curved surfaces, high density codes printed on very small items and bar codes in all types of conditions — from smudged to scratched and poorly printed. Now, you can give your healthcare workers the ability to scan them all with the ds4308-hc. This feature-rich next generation 2d imager resets the bar for scanning performance, scanning range, versatility and ease-of-use. The result? The priceless peace of mind that the right patient received the right medication and the right test results, every time. The ds4308-hc — the ideal companion for laptops on workstation-on-wheels (wows) and other types of carts in your hospital.

PRZM Intelligent Imaging technology for next generation performance

Resets the bar for 2D imaging by improving decode performance and snappiness, ensuring the virtually instant capture of bar codes required in the mission critical world of healthcare.

Megapixel sensor and advanced algorithms enable first time capture of any bar code, on any medium — in virtually any condition

Give your healthcare workers true peace of mind with the ability to scan virtually any 1D, 2D or PDF417 bar code, as well as the many challenging bar codes in healthcare — including the tiny dense codes wrapped around the curved surface of a vial to bar codes that are stained or smudged.

Largest “sweet spot” for can’t-miss point-and-shoot scanning simplicity

A decode range allows healthcare workers to scan any bar code type at any density nearer and farther than any other scanners in its class, making scanning truly second nature. And with omni-directional scanning, healthcare workers never need to waste valuable time aligning bar code and scanner.

Withstands constant disinfecting

IP42 sealing and a specially designed disinfectant-ready plastic housing allow safe wipe-down with a wide variety of harsh chemicals to help prevent the spread of germs.

Unsurpassed aiming technology

The crisp and bright aiming dot has the reach and brightness needed to ensure the fast capture of data.

Durable design for superior uptime

Built to survive a 6 ft./1.83 m drop to concrete, the DS4308-HC delivers reliable operation, despite the inevitable everyday drops.

THE DS4308-HC IDEAL FOR...

- Medication administration
- Blood product administration
- Specimen tracking
- Medication tracking in the pharmacy and on the pharmacy cart
- Electronic healthcare record access
- Patient identification

COMPLIMENTARY MANAGEMENT TOOLS

Simplify and reduce the cost of everyday management with our nocost tools. 123Scan2 and Scanner Management Service (SMS) work hand-in-hand to reduce management time and cost by automating initial configuration and enabling remote management of your DS4308-HC scanners.

Day and night 'do-not-disturb' modes

Healthcare workers can choose to mix and match the decode feedback that is right for the moment: visual (green light/red light), haptic (vibration) and an audible tone.

Superior out-of-box experience

The DS4308-HC is up and running almost instantly. Smart auto-host detect cables automatically determine which interface is attached, eliminating the need to scan numerous configuration bar codes. Over 90 international keyboards are hosted within the scanner for easy setup, all around the world.

Easy on the eyes

Thanks to a special LED wavelength and recessed lighting, when a bar code is scanned, the light that is emitted is soft and unobtrusive, preventing eye fatigue and improving the environment for patients and healthcare workers.

GIVE YOUR HEALTHCARE WORKERS THE POWER TO CAPTURE ANY BAR CODE, ON ANY MEDIUM, IN ANY CONDITION — AND MAKE YOUR HOSPITAL A SAFER PLACE.

For more information, visit www.zebra.com/ds4308hc or access our global contact directory at www.zebra.com/contact

SPECIFICATIONS CHART

PHYSICAL CHARACTERISTICS		SYMBOLGY DECODE CAPABILITY	
Dimensions	6.48 in. H x 3.86 in. L x 2.64 in. W 16.5 cm H x 9.8 cm L x 6.7 cm W	1-D	UPC/EAN, UPC/EAN with supplementals, Bookland EAN, ISS N, UCC Coupon Extended Code, Code 128, GS1-128, ISB T 128, Code 39, Code 39 Full ASCII, Trioptic Code 39, Code 32, Code 93, Code 11, Matrix 2 of 5, Interleaved 2 of 5, Discrete 2 of 5, Codabar, MS I, Chinese 2 of 5, GS1 DataBar variants, Korean 3 of 5, ISB T Concat
Weight (w/o cable)	5.71 oz. / 162 g		
Power	5 VDC $\pm$ 10% @ 360 mA (RMS typical)		
Interfaces Supported	USB , RS232, Keyboard Wedge, RS485 (IBM 46xx) , SS I The scanner supports the following protocols over USB : HID Keyboard (default mode), SNAPI, IBM SurePOS (Yellowstone) (IBM Handheld, IBM Tabletop, OPOS), USB CDC, SS I over USB CDC, Toshiba TEC The scanner supports the following protocols over RS232: Standard, Wincor Nixdorf, ICL, Fujitsu, Olivetti, Omron and CUTE	2-D	PDF417, MicroPDF417, Composite Codes, TLC-39, Data Matrix, Maxicode, QR Code, MicroQR, Aztec, Han Xin
PERFORMANCE CHARACTERISTICS		Postal	Australian Post, US PLANET, Royal Mail 4 State Customer, US POS TNET, KIX Code (Dutch), UK Postal, Japan Post, UPU 4 State Postal FICS (Post US4), USPS 4 State Postal (Post US3), Canadian Post (Postbar)
		Minimum Resolution	SR: Code 39 4 mil, UPC 60% 7.8 mil,
Light Source	Aiming pattern: 617 nm LED Illumination: 660 nm LEDs		
Imager Field of View	36° (H) x 22.5° (V)		
Roll Pitch	0 - 360° $\pm$ 65° or greater		

Yaw	± 60° or greater	PDF417 5 mil, Datamatrix 7.5 mil
Print Contrast	20% minimum reflective difference	HD: Code 39 3 mil, UPC 60% 7.8 mil,
Motion Tolerances	Up to 30 in. / 76.2 cm per second	PDF417 4 mil, Datamatrix 5 mil

ACCESSORIES		USER ENVIRONMENT	
Hands-Free Options	Gooseneck Intellistand	Operating Temp.	32° F to 122° F/0° C to 50° C
Power Supplies	Power supplies are available for applications that do not supply power over the host cable	Storage Temp.	-40° F to 158° F/-40° C to 70° C
		Humidity	5% to 95%, non-condensing
		Drop Specification	Withstands multiple 6 ft./1.83 m drops to concrete
		Ambient Light Immunity	Immune to normal indoor lighting up to 1600 Lux; immune to sunlight up to 86,000 Lux
WARRANTY		REGULATORY	
Subject to the terms of Zebra's hardware warranty statement, the DS4308-HC is warranted against defects in workmanship and materials for a period of 5 years from the date of shipment. For the complete Zebra hardware product warranty statement, go to: http://www.zebra.com/warranty		Electrical Safety	UL60950-1 2nd ed, CSA C22.2 No . 60950-1 2nd ed, EN60950-1/IEC60950-1 2nd ed.
		LED Safety	IEC 62471:2006 and EN 62471: 2008
		EMI/RFI	FCC Part 15 Class B, ICES-003 Class B, EN55022 Class B, EN55024, Medical Electrical Equipment: EN60601-1-2
		Environmental	Compliant with RoHS directive 2011/65/EU

RECOMMENDED SERVICES

Enjoy easy access to fast repair and expert support with **Service from the Start**; add “next business day” replacement with **Advanced Exchange**.

DECODE RANGES

SR FOCUS RANGE		TYPICAL WORKING RANGE	
BAR CODE TYPE	SYMBOL DENSITY	NEAR	FAR
Code 39	3.0 mil	1.5 in. / 3.8 cm	5.4 in / 13.7 cm
Code 39	5.0 mil	0 in. / 0 cm	11.0 in / 27.9 cm
PDF417	6.6 mil	1.1 in. / 2.8 cm	8.0 in / 20.3 cm
UPC	13.0 mil	0 in. / 0 cm	28.0 in / 71.1 cm
Data matrix	10.0 mil	2.0 in / 5.1 cm	9.0 in / 22.9 cm
Code 39	20.0 mil	0 in / 0 cm	53.0 in / 134.6 cm

QR	10.0 mil	1.1 in./2.8 cm	8.5 in./21.6 cm
QR	20.0 mil	0.9 in./2.3 cm	16.2 in./41.1 cm

HD FOCUS RANGE		TYPICAL WORKING RANGE	
BAR CODE TYPE	SYMBOL DENSITY	NEAR	FAR
Code 128	3.0 mil	1.0 in / 2.5 cm	3.0 in / 7.6 cm
Code 39	3.0 mil	0.5 in / 1.3 cm	5.8 in / 14.6 cm
Code 39	5.0 mil	0.0 in / 0.0 cm	10.0 in / 25.4 cm
micro PDF	4 mil	1.0 in / 2.5 cm	4.7 in / 11.9 cm
PDF417	6.6 mil	0.2 in / 0.5 cm	7.8 in / 19.7 cm
UPC	13 mil	0 in / 0 cm	16.5 in / 41.9 cm
Datamatrix	5 mil	1.2 in / 3.0 cm	3.5 in / 8.9 cm
Datamatrix	7.5 mil	1.0 in / 2.5 cm	6.5 in / 16.5 cm
Datamatrix	10.0 mil	0.8 in / 1.9 cm	8.2 in / 20.8 cm
Code 39	20.0 mil	0 in / 0 cm	30.0 in / 76.2 cm
QR	10.0 mil	0 in / 0 cm	7.0 in / 17.8 cm
QR	20.0 mil	0.5 in / 1.3 cm	11.0 in / 27.9 cm

123Scan²

Programs scanner parameters, upgrades firmware, provides scanned bar code data and prints reports.

www.zebra.com/123scan2

Scanner Management Service (SMS)

Remotely manages your Zebra scanner and queries its asset information.

www.zebra.com/sms

Scanner SDK

Generates a fully-featured scanner application, including documentation, drivers, test utilities and sample source code.

www.zebra.com/software



ZEBRA

Part number: SS-DS4308HC. Printed in USA 04/15. ©2015 ZIH Corp. ZEBRA, the Zebra head graphic and Zebra Technologies logo are trademarks of ZIH Corp, registered in many jurisdictions worldwide. All rights reserved. All other trademarks are the property of their respective owners.

ZEBRA TECHNOLOGIES